




CARFIL QUALITY
YOUR SUPPLIER FOR ALL LABORATORY NEEDS

68U053 Rat Anesthesia Adaptor



This adaptor integrates the gas anesthesia mask function while holding the rats head firmly. The adaptor can rotate the head to multi-angles without blocking the anesthetic gas delivery.

Parameters

- The D/V adjustment range is 30mm (-20mm`+10mm), with 100µm accuracy.
- The vertically rotatable range is 70° (-35° ~ +35°), with 5° accuracy.
- The horizontal rotatable range is 70° (-35° ~ +35°), with 5° accuracy.
- The horizontal adjustment range is 43,5mm.
- The diameter of the inlet/outlet of gas anesthesia mask is 2mm.

Please make sure to use a safe gas evacuation!



PAVAN SERVICE BVBA

Beyntellus 3 - B-2360 Oud-Turnhout - Tel. +32 (0)14 45 13 10 - admin@carfil.be - BTW BE 0420.681.872

www.carfil.be